

The filter for visual observation of the Nikon A1Rsi in Yamate area

| Name      | Excitation filter (nm) | Dichroic mirror (nm) | Emission filter (nm) |
|-----------|------------------------|----------------------|----------------------|
| DAPI      | 340-380                | 400                  | 435-485              |
| FITC-LP * | 465-495                | 505                  | 510                  |
| TxRed     | 540-580                | 595                  | 600-660              |
| CFP       | 436/20                 | 455                  | 480/40               |
| DAPI      | 340-380                | 400                  | 435-485              |